

技术资料

2638A-101 |10Ω分流器，10个，最大100mA，准确度0.05%



产品概述: 2638A-101 |10Ω分流器，10个，最大100mA，准确度0.05%

The 2638A-101 Current Shunt Resistors are mounted inside the Universal Input Module using the same screw terminals that accept the user's input wiring. This option contains 10 resistors for measuring up to 10 current channels.

The current shunts are 10 Ohm, +/- 0.08 % resistors that support current measurement up to 100 mA. The resistors are placed in series with the circuit to be measured. The voltage across the resistor is directly proportional to the current flowing through it. The data acquisition instrument processes the resultant voltage into an equivalent current for display and recording.

These shunt resistors are compatible with the 2638A-100 input module for the Hydra Series III 2638A. Shunt resistor sets for 2640A, 2645A, 2680A and legacy Hydra, and Hydra series II data acquisition products have different lead spacing requirements on the input module and require the [2620A-101](#) shunt set.

型号



2638A-101

10Ω分流器，10个，最大100mA，准确度0.05%



FLUKE.

Fluke. 让您的工作畅通无阻。

福禄克测试仪器（上海）有限公司 电话：400-810-3435 ©2025 福禄克公司
07/2025

北京福禄克世禄仪器维修和服务有限公司 电
话：400-615-1563 未经许可，本文档禁止修改
福禄克测试仪器（上海）有限公司上海维修中心 电
话：021-54402301, 021-54401908分机269
福禄克测试仪器（上海）有限公司深圳第一特约维修点
电话：0755-86337229